

Machines

Machine	TASKI Intellidose
Subassembly	----

Revision of the electronics, wiring and hosing

TASKI Intellidose has been revised in various terms. High numbers in demands of spare parts have led us to carry out these adjustments.

The layout of the electronics has been modified and it has now a new fork light sensor. It is held by two plastic parts, which now fix and position the hose at the same time. This modification makes the measuring process less critical against external influences such as light or hose tolerances and results in better process reliability.

The connection strands of the electronics are now soldered from the other side. This way the risk of a cable breakage is getting reduced and the assembly simplified.

The hosing has been optimized and equipped with a quick connector. However, this modification is already in place for several months.

Due to the number of improvements we have decided to raise the serial number as of the revised electronics to 30000. From this serial number onward all modifications mentioned are implemented.



New hosing



Revised electronics

Description	Material number	Remarks
Housing	4127307 (62000-31)	Existing spare part number

Service Information

- | | |
|---|--|
| <input type="checkbox"/> Check parts on stock | <input type="checkbox"/> Return defective parts to Münchwilen |
| <input type="checkbox"/> Proactive exchange recommended | <input checked="" type="checkbox"/> NO proactive exchange recommended |
| <input type="checkbox"/> Modification is backwards compatible | <input checked="" type="checkbox"/> Modification is NOT backwards compatible |
| <input type="checkbox"/> Update/modify machines in the field | <input type="checkbox"/> Entitled to warranty |
| <input checked="" type="checkbox"/> Dispose/recycle defective parts | <input checked="" type="checkbox"/> Parts are available ex stock Münchwilen |
| <input type="checkbox"/> Others | |

Produktion

TASKI Intellidose

as of machine number 30000